



BURNDY Catalog Number
UPC Number
Description
Status

TP1010
 7818107108455
 RING 12- 10AWG VINYL
 Active

Web Use
 BURNDY Product Line

Dimensional

Max Insulation Diameter	0.26
Length (in)	1.00
Tongue Type	Ring
Thickness	0.04
B Length (in)	0.34
Pad Width (in)	0.36
Strip Length	19/64

Electrical

Max Voltage Rating	600
--------------------	-----

General

Product Description	Copper Terminal, Ring Tongue, 12-10 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated, Wire strip length: 19/64"
---------------------	--

Other

Bulk Package	BA10E10M
--------------	----------

Physical

Type of Plating	Tin
Connector Type	Terminal
Color Code	Yellow
Insulation Type	Vinyl
Plated (Yes or No)	Y

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Conductor(s)

Copper Solid Size (Range)	12-Max Insul. Dia. Accom.: .260
Copper Stranded (Range)	Color Code: Yellow 12-10

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175