







U214MTBL
100A 4T RT OU MAIN
784572178847

Brand Name:	Milbank
Type:	Ring Type Meter Socket
Application:	Meter Socket With Main And Load Center
Standard:	UL Listed
Voltage Rating:	Up to 240 Volts Alternating Current
Amperage Rating:	100 Continuous Ampere
Phase:	1 Phase
Frequency Rating:	60 Hertz
Size:	4.625H x 25W x 24.75H
Number Of Cutouts:	1
Cutout Size:	100 Ampere Main Breaker
Cable Entry:	Overhead and Underground
Terminal:	Single Mechanical Line Side and Single Mechanical Load Side Connector
Insulation:	Fiberglass with Resin
Mounting:	Surface Mount
Enclosure:	Type 3R, G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity:	4 Terminal
Bypass Type:	Link Bypass
Number of Metered Positions:	1 Position
Equipment Ground:	Ground Lug
Hub Opening:	Twin Small Closing Plates
Line Side Wire Range:	14 AWG - 1/0
Number Receptacles:	0



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	4	STD. MNTG. EMBOSS
B	12	½ SOLID K.O.
C	6	½, ¾ CONC. K.O.
D	1	½, ¾, 1, 1¼ CONC. K.O.
E	3	¾, 1, 1¼, 1½ CONC. K.O.
F	3	1¼, 1½, 2, 2½ CONC. K.O.



Version:

1

All dimensions are +/- 1/16".
 Drawing views are not to scale.

Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.