

# Specs at a Glance

Application	New Construction, Remodel, Retrofit							
Housing	OneFrame; SurfaceFrame; Classic Frames 4", 5", 6", 8"; Surface Mount; Junction Box							
Lumen Output (Power)	750 lm (10.8W), 1000 lm (12.8W)							
Color Quality	93+ CRI, 2-step SDCM							
CCT Options	2700K, 3000K, 3500K, 4000K							
Lifetime (L70)	50,000 hrs							
Input Voltage	120/277V							
Dimming	Down to less than 5% for TRIAC/ELV at 120V, 1% for 0-10V or Lutron® Hi-lume® 1% at 120/277V							
Emergency Lighting	Optional Emergency LED Driver for lighting up to 90 minutes in event of power failure							
Trim Shape	Round, Square, Deep							
Trim Style	Smooth, Baffle, Hyperbolic, Pinhole, Beveled Pinhole, Wall Wash, EM							
Trim Finish	White, Black, Silver (silver reflector, white flange), Alzak (low iridescent reflector, white flange), Custom							
Listings	cULus Listed, ENERGY STAR® qualified, California Title 24 2016 JA8 compliant, UL Listed for Wet Location, DRDHNJD metallic outlet box certified UL514A up to 2 hours fire rating, STC/IIC Sound Rated, IC rated, ASTM E283 certified Air Tight							
Warranty	5 years							



### FRAME-IN KIT (Product Code Example: DRDH + N + JD = DRDHNJD)

PRODUC	PRODUCT CODE APPLICATION		APERTURE		DRIVER		OPTION		
DRDH	Housing	N	New Construction	JD	OneFrame - Deep Junction Box	[Blank]	Integrated TRIAC/ELV	[Blank]	None
						70	0-10V, 750 lm	EM	EM Driver, Integrated Test Switch
						100	0-10V, 1000 lm	EMS	EM Driver, Remote Test Switch
						7C	Lutron LDE1, 750 lm		
						10C	Lutron LDE1, 1000 lm		
						7W	Lutron L3DA3W, 750 lm		
						10W	Lutron L3DA3W, 1000 lm		

#### LIGHT ENGINE (Product Code Example: DRD2M+7+9+27= DRD2M7927)

PRODUC	RODUCT CODE LUMENS (WATTS)			CR		ССТ		DRIVER		
DRD2M	Module	7 750 lm (10.8W)		9	93+ CRI	27	2700K	[Blank]	Integrated TRIAC/ELV	
		10 1000 lm (12.8W)				30	3000K	Α	Alternate Dimming	
						35	3500K			
						40	4000K			

#### TRIM (Product Code Example: DRD2T+R+JD+S+WH=DRD2TRJDSWH)

PRODUCT CODE		SHAPE		APE	APERTURE		/LE	FINISH		OPTION		
DRD2T Trim		R	Round	JD	Deep Junction Box	S	Smooth	WH	White	[Blank]	None	
		S	Square			Н	Hyperbolic	BK	Black	FL	Flangeless	
						Р	Pinhole	sw	Silver Reflector w/ White Flange	EM	Test Switch	
						В	Beveled Pinhole	СС	Custom Color	DCC	Decorative: Closed, Clear	
						W	Wall Wash			DCF	Decorative: Closed, Frosted	
										DCCF	Decorative: Closed, Clear Out, Frosted In	
										DOF	Decorative: Open, Frosted	

## **Dimensions**









