



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Type QP/MP, 3-Pole, 240VAC are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QP/MP Application: Electrical Distribution Standard: UL 489 Voltage Rating: 240V Amperage Rating: 40A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 3P

Number of poles	3
Suitability for operation	Electrical Distribution
Electricity	
Continuous current rated value	40 A
Model	
Product brand name	SIEMENS
Type of electrical connection	PLUG-IN
Mechanical Design	
Depth [in]	12.8 in
Design of the product	QP/MP
Height [in]	3.4 in
Width [in]	3.7 in
General product approval	
Standard	UL 489
last modified:	11/09/2017