



# S9856

9WPLH/LED/840/DR/2P  
9W LED PL 2-Pin; 4000K; 900 Lumens; G24d base; 50000  
Average rated hours; 120 Deg. beam spread



## Features


- Replaces 26 watt CFLs
- Direct Replacement - for use with Magnetic ballasts with no rewiring required. Ballast required.
- Instant on to full brightness / no flickering
- Horizontal operation
- Up to 70% energy saving
- Long life - 50,000 hours
- 5 year warranty

S9856

View:

[Ballast Compatibility Chart](#)

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	Lamp Code	Finish
S9856	045923098567	9	26 watt CFL	PL	G24d	9WPLH/LED/840/DR/2P	Frost
MOL In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Package Type
6-5/8"	900	50000	4000	Cool White	82	120	Box
RoHS Compliant	UL or ETL Listed	UL Classification				Warranty	
Yes	Yes	cULus Classified - Damp Location Rated				<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

