

*Hoffman*

Continuous Hinge with Clamps, Type 4X

Catalog Number: A16H1608ALLP

Bulletin Number:

- A4A

Material:

- Aluminum



Model Code:

- 24280

Ship Wt. Std. Pkg. (lbs):

- 14.0

Interchangeable:

- False

Industry Standards:

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997 cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997 NEMA/EEMAC Type 3R, 4, 4X, 12, 13 CSA File No. 42186: Type 4, 4X, 12 IEC 60529, IP66 *Meets NEMA Type 3RX requirements*

Description

Lightweight enclosure protects components and controls in highly-corrosive indoor or outdoor environments such as petrochemical processing plants, sewage treatment plants and marine environments.

Applications:

Lightweight enclosure protects components and controls in highly-corrosive indoor or outdoor environments such as petrochemical processing plants, sewage treatment plants and marine environments.

Specifications:

- Type 5052 H-32 aluminum
- Seams continuously welded and ground smooth
- Rolled lip around three sides of door and all sides of enclosure opening
- Stainless steel door clamp assemblies
- Door is easily removed by pulling stainless steel continuous hinge pin
- Data pocket is high-impact thermoplastic
- Hasp and staple for padlocking
- Panel screws are plated
- Tapped pads provided for mounting optional panels
- Oil-resistant gasket

Finish:

Enclosures are unpainted. Door fronts have smooth brushed finish.

Modifications and Customizations:

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

Accessories:

- Fast-Operating Clamp Assembly

- Panels for Type 3R, 4, 4X, 12 and 13 Enclosures
- Rack Mounting Angle Kit - L Style
- Junction Box and Wall-Mount Enclosure Swing-Out Panel Kit
- Terminal Block Kit Assembly for Type 4, 12 and 13 Enclosures
- Steel and Stainless Steel Window Kits

Notes:

Purchase panels separately. Optional composite and aluminum panels are available for most sizes.

Technical Data

Continuous Hinge with Clamps, Type 4X

Catalog Number	A16H1608ALLP
A mm	406
B mm	406
C mm	203
F mm	76
Panel Size D x E mm.	330 x 330
Conductive Panel	A16P16G
Aluminum Panel	A16P16AL
Steel Panel	A16P16
Number of Panel Mounting Studs	4
Data Pocket Size mm	152 x 152

Certifications

 EU Certification

 UL Certification

Documents

 DOC

 3D STEP CAD

 2D DXF CAD

 Spec Sheet
















 Instruction Manual

 Instruction Manual

 Instruction Manual (ROHS)

 Dimension Drawing

Accessories

Item		
	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures	A16P16
	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures	A16P16AL
	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures	A16P16G
	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures	A16P16SS6
	Clamp Block Kit	ACBK6SS
	Fast-Operating Clamp Assembly	AFC412SS
	Steel, Stainless Steel and Non-Metallic Window Kits	APWK116NFNM
	Steel, Stainless Steel and Non-Metallic Window Kits	APWK53NFNM
	Steel and Stainless Steel Window Kits	APWK53NFSS
	Steel and Stainless Steel Window Kits	APWK711NFSS
	Steel, Stainless Steel and Non-Metallic Window Kits	APWK95NFNM
	Steel and Stainless Steel Window Kits	APWK95NFSS
	Type 4 and 4X Deep-Hinged Window Kits	AWDH1612N4SS
	Type 316 Stainless Steel Door Stop Kit	ADSTOPKSS6
	Remote Door Switches	ALFSWD
	Industrial Corrosion Inhibitors	AHCI10E



Industrial Corrosion Inhibitors

AHCI1DV



Industrial Corrosion Inhibitors

AHCI238S



Industrial Corrosion Inhibitors

AHCI240R



Industrial Corrosion Inhibitors

AHCI5E



Industrial Corrosion Inhibitors

AHCI60R



Terminal Straps for Type 4, 12 and 13 Enclosures

A16T



LED Light Kit

LEDA1S35



LED Light Kit

LEDA2S35



HOL-SEALERS Hole Seals

AS050



Continuous Hinge with Clamps, Type 4X

A16H1608ALLP



Bracket Assembly for Type 4, 12 and 13 Enclosures

A16NTMA2



Junction Box and Wall-Mount Enclosure Swing-Out Panel Kit

ANADFK



Threaded Panel Extenders

APE050



Threaded Panel Extenders

APE100



Terminal Strap Support Kit

ATZ

