



GE
Lighting

69119 - GE LED A19

LED10DA19/830

- ☞ Energy efficiency and long life mean fewer lamp replacements versus standard incandescent or halogen light sources
- ☞ 60 watt replacement using only 10 watts
- ☞ Light pattern similar to traditional incandescent bulbs.
- ☞ Great for frequently used fixtures
- ☞ Omnidirectional
- ☞ Energy Star Rated

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Dimmable	Yes
Lamp Type	A19
Primary Application	General Purpose
Product Color	White
Product Technology	LED
Rated Life - Min	15000 h
Rated Life (Hours)	15000 h
Dimmable / Non-Dimmable	Yes
Lamp Count	1
Life in Years	13.7 yr
Replacement Watts	0 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.2
Base	E26
Bulb Shape	A19

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	800 lm
Color Rendering Index-CRI	80
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	69119
Description	LED10DA19/830
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168691192
Standard Package GTIN	00043168691192
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168691192
Standard Package GTIN	10043168691199
No Of Items Per Sales Unit	
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	

DIMENSIONS

Bulb Max Overall Length-MOL	4.4 in
-----------------------------	--------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V
Rated power (Watts)	10 W