

Item #  
P1193-077-L

Product Family Name:  
Diamonds LED

Category:  
BATH

Certification  
3195125

Patents:

Notes:

UPC Code:  
844349019954

Finish:  
Chrome

Category Type:  
Bath



Image File Name: P1193-077-L.jpg



MEASUREMENTS

Width: 32	Length: No	Height: 5	Extension: 3
Height Adjustable: Min Overall Height:		Max Overall Height:	Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 6.53
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom: 2.5
Backplate Width: 7.0	Backplate Height: 5.0	Center to Top: 2.5	

LAMPING

No. of Bulbs: 1	Light Type: 32W LED MODULE			
Max Bulb Wattage: 33	Socket: LED			
Dimmable: Yes	Ballast:	Rated Life Hours: 30000	Photocell Included: No	Bulb/LED Included: Y
Bulb/LED Included: Yes	Color Temp.: 3000	CRI: 92	Initial Lumens: 2707.0	Delivered Lumens: 2085.0



SHIPPING

Description: Clear	Material: GLASS	
Part No.: PG1193-1	Quantity: 1	
Width: 2.25	Height: 1.75	Length: 31.38

Carton Width: 7.0	Carton Height: 6.375	Carton Length: 35.625
Carton Weight: 7.83	Carton Cubic Feet: 0.92	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack:

LED



ADA  
Compliant



Damp  
Location



ETL  
Intertek

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.