

F3136/8DWK/SGM: 8 - Light Island Chandelier



Dimensions:

Length:	46"	Overall Height:	73 3/4"
Width:	16"	Wire:	240" (color/Brown)
Height:	16 1/2"	Mounting Proc.:	Center Lock-Up
Weight:	27.4 lbs.	Connection:	Mounted To Box

Bulbs:

8 - Medium A19 60w Max. 120v - Not included

Material List:

1 Body - Steel - Distressed Weathered Oak / Slate Grey Metal
 8 12" Stem - Steel - Slate Grey Metal
 2 6" Stem - Steel - Slate Grey Metal

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (F3136-8)

Collection: Angelo

UPC #: 014817569650

Finish: Distressed Weathered Oak / Slate Grey Metal (DWK/SGM)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Clear	8				7	4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/4	12 3/4	5 1/2			

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F3136/8DWK/SGM	1	014817569650	50.5	19.25	20.25	11.392	37.5	250	Yes

NJ Pallet		6		48	40	64.5	71.667	190.5		No
NV Pallet		6		48	40	64.5	71.667	190.5		No