

Low-Profile Strain Relief Cord Connectors

Zinc die-cast. Liquid-tight • Oil-tight.
Furnished with sealing ring and locknut.

Cord Grips



CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	CORD RANGE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
LPCG503Z*	50352	1/2	.100-.300	25	100	1.792	.630	1.042
LPCG50Z*	36110	1/2	.200-.472	25	100	1.792	.630	1.042
LPCG507Z	50356	1/2	.385-.750	25	100	2.178	.517	1.305
LPCG753Z*	36105	3/4	.100-.300	10	50	1.963	.570	1.042
LPCG754Z	50764	3/4	.240-.472	10	50	1.963	.570	1.305
LPCG757Z	50766	3/4	.385-.750	10	50	2.250	.600	1.305



* UL not applicable for under .240 wire diameter -- wire strength will not meet UL's 35lb pullout test requirement for the fitting.

PATENTED.

