HALO®

DESCRIPTION

An economical thermally protected square aperture fixture for use with 150W A21 incandescent lamps. The H2T is complete with a built-in aluminum reflector, plaster frame, and feed-through junction box. Ten different trim styles are available for the H2T housing.

APPLICATION

Suitable for either residential or commercial applications, the H2T provides an economical housing choice with square trims.

Catalog # Type Project Comments Prepared by Date

SPECIFICATION FEATURES

A ··· Reflector

One piece die formed 20 gauge aluminum reflector.

B.-Plaster Frame

20 gauge steel. Reflector adjusts 3/4" in plaster frame

C...Socket

Porcelain socket with nickel plated screw shell for medium base incandescent lamps.

D...Bar Hangers

Fully Adjustable "Nailess" Bar Hangers fit between 24" joists and span 24" T-Bars. Housing may be positioned at any point along length of fully extended Hanger Bars and may be repositioned 90°. Bar Hangers fit onto T-Bar spine for quick alignment and can be permanently secured with optional TB-7 T-Bar Clip.

E.-Junction Box

UL listed for through branch circuit wiring with eight no. 12 branch circuit conductors suitable for at least 90°C (Four in, four out).

Six easy to remove 1/2" pryouts allow junction box access from top and sides.

Four Romex pryouts with integral strain relief simplify Romex installation

Thermal Protector

Provides protection against improper use of ceiling insulation.

Labels


- U.L. listed for damp location
- U.L. listed for Feed Through
- · C.S.A. certified
- IP rated



H₂T

11" Square Non-Insulated Ceiling Recessed Housing

SQUARE TRIMS



FOR USE IN NONINSULATED CEILINGS
OR
INSULATED CEILINGS
BUT INSULATION
MUST BE KEPT 3"
FROM ALL SIDES OF
FIXTURE

ADV042527 Supersedes ADV000328

ORDERING INFORMATION

SAMPLE NUMBER: H2T-20P

Order housing, trim and accessories separately.

Housing

H2T=11" Square Non-Insulated Ceiling Housing

Trims

LENSES AND DIFFUSERS



Albalite Lens 150W A21 20P=Albalite Lens - White Frame 11 5/8" Square (295mm)

Glass Drop Diffuser

Fresnel Lens

150W A19 21GP=Glass Drop Diffuser - White Frame 11 5/8" Square (295mm)



21

150W A19 23P=Fresnel Lens, White Frame 11 5/8" Square (295mm)



All-Glass Diffuser 150W A19 25=Glass Diffuser 11 5/8" Square (295mm)

11 5/8" Square (295mm)



Regressed Drop Opal 150W A19 26P=Regressed Drop Opal Lens with Black Baffle 11 5/8" Square (295mm)



Albalite Splay 150W A19 120P=Glass Diffuser with White Splay Listed for use as Shower Light



Fresnel Splay 150W A19 123P=Fresnel Iens with White Splay Listed for use as Shower Light 11 5/8" Square (295mm)



Glass Drop Opal Splay 150W A19 126GP=Glass Drop Opal Splay Listed for use as Shower Light 11 5/8" Square (295mm)

Accessories

Step Down Transformer Steps 277V line voltage down to 120V fixture operating voltage. 150VA max. H277=150VA Max.

