



9351-NFR



VIDEO

Product Description

4" dia. round fan support box for use with nonmetallic sheathed cable

Brand: fiberglassBOX™
Catalog #: 9351-NFR

Width: 4 in.
Depth: 2-7/16 in.
Volume: 22.5 cu. in.
Type of Installation: New Work
Round Ceiling Box

Carton Quantity: 48
Carton Weight: 26 lb.

UPC: 085339650010
UNSPSC: 39121316
Country of Origin: United States of America

FEATURES

Machine tapped fixture holes, rigid hard box construction, no distortion with high temperatures, shatter resistant with low temperatures, Speed "K" Clamps bulk packed

APPLICATION

New work residential construction 2 HR fire resistive walls and ceilings (35 lbs. fan support and 50 lbs. fixture support)

STANDARDS

ANSI / UL 514C: File No. E30594



FIRE CLASSIFICATION

Fire Test of Building Construction Materials

ANSI / UL 263: File No. CEYY.R9379 (Category / File No.)

Note: Products must also be certified to: ANSI / UL 514C

Fire Resistance Classification in Wall Assemblies 2-Hours or less

Shall be separated by a horizontal distance of not less than 3 inches

Fire Resistance Classification in Floor-Ceiling Assemblies 2-Hours or Less

Distance between boxes in adjacent cavities may be reduced to 5 ½ inches

Note: For more details please refer to the UL fire resistive directory and Allied Moulded's CEYY.9379 (Outlet boxes and fittings classified for fire resistance)

COLOR

Beige/tan

MATERIAL

Fiberglass reinforced polyester BMC

MOUNTING

Nail-on with fetter ring nails

ADDITIONAL MATERIALS

Carbon steel fasteners

Plated carbon steel fasteners

Polyvinyl chloride clamps

SUPPORT RATING

50 lbs fixture support and 35 lbs fan support