



Sunlite 125 Watt R40 R40 Infrared Heat Lamp, Medium Base, Clear

- 125-Watt. 125-Volt
- N/A Lumens
- 2000 Hours Average Lamp Life
- Medium Base
- 125R40/H/CL



General Characteristics

Bulb	R40
Lamp Type	R40 Infrared Heat Lamp
Lamp Life Hours	2,000 Hours
Bulb Finish	Clear
Base	Medium (E26)
Life (based on 3hr/day)	1.8 Years
Estimated Energy Cost	\$15.06 per Year
Dimmable	True

Electrical Characteristics

Watts	125
Volts	125

Light Characteristics

Color Temperature	3200K
--------------------------	-------

Product Dimensions

MOL (in)	6.75"
Diameter (in)	4.85"
Item Dimensions (in)	(W) 4.84 (H) 6.68 (D) 4.84
Package Dimensions (in)	(W) 4.80 (H) 6.40 (D) 4.80

Product Data

Item Number	03687-SU
Case Quantity	12
Barcode on SKU	653703036878
Barcode on Case	817777036886
Brand	SUNLITE
Description	125R40/H/CL