



S8600

1.6JC/G4/LED/3000K/12V/D
1.6 watt; T3 JC LED; 3000K; G4 base; 12 volts; Carded

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen G4 lamps.

Dimensions: Height 36.3 mm (1.43 in.) x Width 10 mm (0.39 in.)
x Depth 10 mm (0.39 in.)



S8600

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	Lamp Code	Dimmable/Non-Dimmable
S8600	045923086007	12	1.6	T3	G4	1.6JC/G4/LED/3000K/12V/D	Dimmable

Suggested Dimmers	Finish	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg
Compatible dimmers for S8600	Clear	200	25000	3000	Soft White	80	360

Pack	Package Type	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification
48/12	CD/1	Lawful for sale in California	Yes	Yes	cETLus - Damp Location Rated



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

