



# S9767

80W/LED/HID-HB/5000K/100-277V

80 watt - LED HID Hi-Bay Replacement; 5000K; Mogul extended base; 100-277 volts

## Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- Damp location
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C
- Safety chain included
- Not approved for enclosed fixtures

## Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V



S9767

Item Number	Product Line	UPC	Input Voltage	Watts	HID Equivalent	Base	ANSI Base
S9767	Hi-Pro	045923097676	100 - 277	80	400W	Mogul	E39

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
80W/LED/HID-HB/5000K/100-277V	Non-Dimmable	Frosted	10-13/16"	6-11/16"	7600	25000	5000

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification
Natural Light	80+	120	4	Box	Yes	Yes	UL - Listed

## Warranty

[5 Year Limited](#)



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051