

886-HC1



8x6x8 Hinge Cover Type 1 UL Listed Steel Knockouts ANSI 61 Gray
Flush Pull Ring Formed Hinges Mounting Holes In Back

SPECIFICATIONS

Brand Name	Milbank
Type	Hinge Cover
Application	Enclosure for Mounting Electrical Equipment
Standard	UL Listed
Number Of Outlet	0
Material	Steel with Powder Coat Finish
Size	8 In x 6 In x 8 In
Color	ANSI 61 Gray
Construction	Welded
Knockouts	Knockouts
Mounting	Wall Mount
NEMA Rating	Type 1
Hinge Type	Formed Stainless Hinges



Top	Plain Top
Door	1 Door
Latch	Flush Pull Ring for Opening
Support	Formed and Spot Welded
Height	8 IN
Length	6 IN
Width	8 IN

IMPORTANT NOTICE: Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

