



USB CHARGERS WITH DUPLEX 15A TAMPER-RESISTANT OUTLETS, WHITE

TM826USBWCC6 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® USB charging solutions let you charge more of your devices without the need for bulky AC adapters.

radiant® Screwless Wall Plate not included.

For detailed information on USB Charging Devices, visit our [USB Charging page](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Part of the all-new radiant® collection.
- Charge two devices simultaneously while also using receptacles.
- Compatible with USB 2.0 & 3.0 compatible devices.
- Total charging capacity of 3.1A.
- AC receptacles are tamper-resistant to meet NEC®
- Patented shutter system—now with black “invisi-shutters” for an invisible effect preferred by end users—prevents improper insertion of foreign objects.
- Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire for installation flexibility.
- Accepts standard Pass & Seymour wall plates and radiant® Screwless Wall Plates.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Special Features: 3.1 Amps of total charging capacity

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42; C22.2 No. 223

CSA Standard: Yes

cULus: Yes

UL Listing No: UL498; UL1310
UL Standard: Yes

DIMENSIONS

Depth (US): 1.39"
Height (US): 2.67"
Width (US): 1.69"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
Volts: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA