

FEATURES & SPECIFICATIONS

INTENDED USE — The new Z series straight-blade louver (SBL) products offer engineers and specifiers a contemporary designed lighting fixture which provides the ideal balance of appearance, performance and efficiency. Versatile for a wide range of spaces from retail, commercial, merchandising and task applications, this new low-profile SBL series provides the perfect solutions for general and reduced-space areas.

CONSTRUCTION — All metal components are constructed of code-gauge cold-rolled steel and are painted with a 92% reflective enamel powder paint finish. Precision-designed blade assemblies are positively retained to the housing with safety cables for ease of cleaning and re-lamping. Conveniently located top access plate and KOs provide contractors easy wiring connections.

Finish: All parts are painted after fabrication with a high-gloss, white enamel finish (white standard). Five-stage iron phosphate pretreatment ensures superior paint adhesion and rust resistance. Similar to the Z strip, three additional paint finishes are available; black (MB), smoke gray (SKGY) and galvanized (GALV). For RAL finishes; consult factory

OPTICS — Straight-blade louvers available in 48" and 46" increments, either solid or perforated versions. Housing design is offered in solid and two different uplight offerings (8% and 5%). Special uplight versions are available; consult factory.

ELECTRICAL — Thermally protected, resetting, Class P, HPF non-PCB, UL listed. Suitable for damp locations. AWN, TFN or THHN wire used throughout, rated for required temperatures.

INSTALLATION — All SBL versions come fully assembly in a tab lock carton for simple, easy installation. Additionally for continuous-row application, each SBL includes our patented three-point row connector and housing clips for straighter, faster row mounting.

This product series can be surface or stem mounted.

LISTINGS — Listed for 25° C ambient temperature.

WARRANTY — 1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx .

Note: Specifications subject to change without notice.

Actual performance may differ as a result of end-user environment and application.

Catalog Number	
Notes	
Туре	



Low-Profile Straight-Blade Louver



Z-SBL

T8 or T5 Linear Lamps 1 or 2 Lamps


Specifications


Length - T8: 48 (121.9)

or 96 (243.8) Length - T5: 46 (116.8)

or 92 (233.7) Width: 6-9/16 (16.7)

Depth: 3-15/16 (10)





All dimensions are inches (centimeters) unless otherwise noted.

ORDERING INFORMATION

For shortest lead times, configure products using bolded options.

Example: Z 1 32 SBL MVOLT GEB10IS

Z												
	Number of lamps	Lamp typ	e	Louver		Voltage	Ballast		Options		Finish	
Z Low profile For tandem double-length unit, add prefix "T". Ex: TZ	1 2 Not included.	32	28W T5 (46") 32W T8 (48") 54W T5HO (46")	SBLP SBLAS SBLAS SBLPAS SBLPAS	Solid-blade louver Perforated-blade louver Solid-blade louver, 8% uplight Solid-blade louver, 5% uplight Perforated-blade louver, 8% uplight Perforated-blade louver, 5% uplight Perforated-blade louver, 5% uplight	MVOLT 347 Others available.	GEB10RS GEB10PS OS10PS	T8 electronic ballast, <10% THD, instant start (T8 only) T8 electronic ballast, 10% THD, rapid start T5 electronic ballast, <10% THD, programmed start OSRAM® T5 electronic ballast, <10% THD, programmed start	SSR GLR GMF PLR_ TILW EL55 EL65 CSA NOM MSI MSI360 MSE360LBZ	MIRO® 4 specular insert Internal fast-blow fuse (add X for external)¹ Internal slow-blow fuse (add X for external)¹ Plug-in wiring; specify number of branch circuits and hot wires (A=black; B=red; C=blue; AB or AC) Tandem in-line wiring Emergency battery pack (nominal 390-700 lumens); consult factory for additional battery pack (nominal 390-700 lumens)¹² Emergency battery pack (nominal 390-700 lumens)¹² CSA Certified NOM Certified Aisle motion sensor³ 360° motion sensor; for mounting within row or at end of row	(blank) MB GALV SKGY	White Black Galvanized Smoke gray

Accessories: Order as separate catalog number.							
	HC36	Hanger chain, 36"	HC36	Hanger chain, 36"	ZAC120	Aircraft cable, 120"	
	SQ_	Swivel-stem hanger (specify length in 2" increments)	ZACVH	Aircraft cable with hook	ZACF120	Aircraft cable with feed, 120"	
	1B	Ceiling spacer; spaces fixture 1-1/2" to 2-1/2" from ceiling 3	ZAC72	Aircraft cable, 72"	ZAC144	Aircraft cable, 144"	
	ZSPRG	Tong and T-grid hanger (for 15/16" T-grid)	ZACF72	Aircraft cable with feed, 72"	ZACF144	Aircraft cable with feed, 144"	

Notes

- 1 Specify voltage (available with 120/277V).
- 2 Not available with CSA Certified.
- 3 For unit mounting, order two per fixture. For row mounting, order one per fixture plus one per row.

INDUSTRIAL Z-SBL-T8T5

Z-SBL Straight-blade Louver Striplight

MOUNTING DATA

For unit or row installation; surface or stem mounting.

Unit installation — Minimum of two hangers required.


Row installation — One hanger per channel plus one per row required.

Review local codes when installing any product, as the minimum of 1 hanger per fixture may not satisfy your local building code.










One-lamp T8

DIMENSIONS

All dimensions are inches (centimeters).



PHOTOMETRICS

One-lamp T5

Consult factory.

INDUSTRIAL:



Z-SBL-T8T5

(16.6)

©2010-2017 Acuity Brands Lighting, Inc. All rights reserved.

Two-lamp T8

(16.6)

Two-lamp T5