

F3133/5DWK/SGM: 5 - Light Chandelier



Dimensions:

Diameter:	24"	Overall Height:	86 1/2"
Height:	24 1/2"	Wire:	180" (color/Brown)
Weight:	18.6 lbs.	Chain:	60"
		Mounting Proc.:	Center Lock-Up

Bulbs:

5 - Medium A19 60w Max. 120v - Not included

Material List:

1 Body - Steel - Distressed Weathered Oak / Slate Grey Metal

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (F3133-5-F3134-6-F3135-9)

Collection: Angelo

UPC #: 014817569629

Finish: Distressed Weathered Oak / Slate Grey Metal (DWK/SGM)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Clear	5				7	4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/4			5		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F3133/5DWK/SGM	1	014817569629	27.5	27.25	11.25	4.879	20.5	175	Yes

NJ Pallet		13		48	40	75	83.333	266.5		No
NV Pallet		13		48	40	75	83.333	266.5		No