



S9761

18W/LED/PAR38/4000K/100-277V
18 watt; LED PAR38; 4000K; 25' beam spread; Medium base;
100-277 volts

Features

- High efficiency 100LPW
- Replaces Halogen and ceramic metal Halide lamps
- Long life
- Non-dimmable

Available February 2017



S9761

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	ANSI Base	Lamp Code		
S9761	045923097614	100-277	18	PAR38	Medium	E26	18W/LED/PAR38/4000K/100-277V		
Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color		
Non-Dimmable	White	5"	4-3/4"	2000	50000	4000	Cool White		
CRI	Beam Spread Deg	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed	UL Classification		Warranty	
83	25	Box	ENERGY STAR	Yes	Yes	cULus - Dry Location Rated		5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

