



LED11.5WT8/48/840-G7DR



Description	GLASS DIRECT FIT DLCV4.1 T8 4FT 11.5W-1800LM 4000K 80CRI EMERGENCY/NON-DIM
Ordering Code	60444
UNSPSC Code	39112102

Specifications

Voltage Rating	120~277
Voltage Type	AC
Watts	11.5
Lumens per Watt	156
Base Type	G13
Bulb Type	T-8
MOL in/mm	47.78/1213.6
Length	4'
MOD in/mm	1.02/26
Lumens	1800
CT deg K	4000
CRI	80+
Rated Life	50000
Special Desc	NOT COMPATIBLE WITH ALL BALLASTS. SEE eiko.com FOR LIST OF TESTED BALLASTS.
Ambient Operating Temp Range	-20° C (-4° F) to 45° C (113° F)

[watch](#) > [like](#) > [follow](#)



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335