

Arkwright Collection  
Arkwright LED Fan Fixture WHT  
338203WH (Textured White)



Dimensions

|        |       |
|--------|-------|
| Height | 2.75" |
| Width  | 7.50" |

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_

Ordering Information

|                    |                      |
|--------------------|----------------------|
| Product ID         | 338203WH             |
| Finish             | Textured White       |
| Available Finishes | AP, OBB, PN, WHT     |
| Collection         | Arkwright Collection |

Photometrics

|                       |       |
|-----------------------|-------|
| Kelvin Temperature    | 3000K |
| Color Rendering Index | 80    |

Specifications

|                      |                   |
|----------------------|-------------------|
| Material             | Steel             |
| Diffuser Description | Etched Cased Opal |

Electrical

|                |   |
|----------------|---|
| Dimmable       | Yes   |
| Dimmable Notes | Recommended for use with Kichler Fan Controls |
| Voltage        | 120V  |

Qualifications

|              |  |
|--------------|--|
| Safety Rated | Dry  |
| Warranty     | <a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a> |

Primary Lamping

|                        |            |
|------------------------|------------|
| Light Source           | LED        |
| Lamp Included          | Integrated |
| # of Bulbs/LED Modules | 1          |
| Initial Lumens         | 1600       |
| Delivered Efficacy     | 94         |
| Max or Nominal Watt    | 17W        |