

P6341 Flood Light With Motion

Wall mounted • Wet location listed



Description:

The two-light Security light with motion sensor is ideal for residential and commercial applications. Each tempered glass head has over 1,000 lumens and is adjustable. The motion sensor has 180 degree coverage, center focus range to 72 feet, Time On, Sensitivity and Distance adjustment with Night/Day or night operation. This fixture saves energy and maintenance over traditional lighting sources.

Specifications:

- Metallic Gray (-82) (Powder Coat Paint)
- Die-cast aluminum construction
- Tempered glass lens
- Two adjustable heads.
- 180 degree motion sensor.
- 2104 lumens, 79 lumens/watt.
- Time On, Sensitivity and Distance adjustment.
- Backplate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
-

Performance:

Number of Modules	2
Input Power	26.6w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	2104/79 (LM-79) per module
CCT	3000 K
CRI	83
Life (hours)	60,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15 Class B
Min. Start Temp	-20 °C
Max. Operating Temp	40 °C
Warranty	5 year warranty
Labels	cCSAus Wet location listed

P6341-82-30K

Images:



Dimensions:

- (A) Width: 12-3/4"
 (C) Depth: 5"
 (B) Height: 6-1/2"

