



Powering Business Worldwide

pe.eaton.com

Eaton Bussmann series high speed North American fuse

FWH-60B

UPC:051712795784

Dimensions:

- **Height:** .5 IN
- **Length:** 4.5 IN
- **Width:** 3.5 IN

Weight:.693 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** FWH, North American style
- **Application:** DC common bus, DC drives, power converters/rectifiers, reduced voltage starters
- **Voltage Rating:** 1000 Vdc
- **Interrupt Rating:** 200 kAIC 1000 Vac, 50 kAIC at 500 Vdc
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Current Rating:** 60A RMS
- **Pre Arc (I²T):** 210
- **Clearing (I²T):** Clearing at 500V: 900
- **Connection:** Blade end X blade end
- **Watt Losses:** 9.9W
- **Mounting:** Stud

Supporting documents:

- [Product Catalog](#)
- [60A 500V AC TAG FUSE](#)

Certifications:

- CSA Certified
- UL Recognized



Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.