

LED9WA19/OMN/840K-DIM-G7 2PK



Description	4000K LED Litespan A19 Omni-directional 9W-800lm Dim 80CRI 4000K E26 120VAC 2 Pack
Ordering Code	60426
UNSPSC Code	39101628

Specifications

Voltage Rating	120
Voltage Type	AC
Watts	9
mA	80
Lumens per Watt	88.88
Base Type	Medium Screw (E26)
Bulb Type	A-19
MOL in/mm	4.41/112.00
MOD in/mm	2.36/60.00
Lumens	800
CT deg K	4000
CRI	80
Beam Angle	Omni
Rated Life	15000
Replaces	LED9WA19/300/840K-DIM-G6
Equivalent	60W A19 Incandescent
Ambient Operating Temp Range	-20° C (-4° F) to 40° C (104° F)
Approvals	cULus, Energy Star

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335