

Vassar Collection

52 Inch Vassar LED Fan WHT

330002WH (Textured White)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____

Product Information

Product ID	330002WH
Finish	Textured White
Blade Finish	White/Silver
Collection	Vassar Collection

Airflow, Power and Efficiency

Speed	RPM	CFM	CFM/ Watt	Amps	Watts
High	178	5041	91	.47	55
Med	128	3415	117	.4	29
Low	83	2214	188	.29	12

Specifications

Number of Blades	3
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	52"
Blades Reversible	No
Blade Material	Wood
Optional Blades Available	No
Downrod 1	1.00 OD X 4.00

3 Speed Wall Control Ltd Function - In project applications using multiple ceiling fans, alternative remote controls may be required. Please contact Kichler Advanced Product Solutions at 844-542-4537 to confirm your project requirements.


Primary Control System	
Remote Included	No
Wall Control Included	Yes
Low Ceiling Adaptable	No
Lead Wire Length	78.00"
Motor Size	153MM X 17MM
Motor Type	AC INDUCTION

Downlight

Downlight Included	Yes
Light Source	LED
Downlight Bulb Included	Included
Downlight Bulb Type	LED
# of Bulbs/LED Modules	1



Dimensions



Downrod	A	B	C	D
1.00 OD X 4.00	15.00	11.00	8.75	6.25

Available Finishes

Finish	Fixture	Glass	Blade 1	Blade 2
Brushed Nickel	330002NI	ETCHED CASED OPAL	SILVER	WALNUT

Vassar Collection

52 Inch Vassar LED Fan WHT

330002WH (Textured White)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____

Finish	Fixture	Glass	Blade 1	Blade 2
Olde Bronze	330002OZ	ETCHED CASED OPAL	CHERRY	WALNUT
White	330002WH	ETCHED CASED OPAL	WHITE	SILVER

Watts	55/29/12
Initial Lumens	1600
Glass Description	Etched Cased Opal
Optional Light Kit Available	No
Efficacy (LMIW)	94
Kelvin Temperature	3000 K
Color Rendering Index	80

Safety Listings & Certifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Installation

Installation requirements	The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""
Electrical Requirements	120V 60Hz AC
Hanging Weight	17.20 LBS
Minimum Distance Between Bottom Of Fan Blade To Floor	7 feet