



Home Office PH100-61-F

sku#: PH100-61-F

Home/Office Polished Brass Floor Lamp

Dimensions: 34"-48"H x 10.5"W x 17.5"D

Base Diameter: 10.5" diameter

Bulb Type: 1-60W-T10 medium base (not included)

Switch Placement: On socket

Shade Size: 10" Metal

Country of Origin: China

Ships Via: FedEx

Safety Rating: UL Listed

CA Title 20 Compliant: Yes, when purchased with CFL