



S9389

6.5PAR16/LED/40'/5000K/120V
6.5 watt PAR16 LED; 5000K; 40' beam spread; Medium base;
120 volts

Features

- Direct replacement for 60W
- Halogen PAR16 lamps
- Dimmable
- Damp location
- Approved for enclosed fixtures
- Long life - 25,000 hours
- High efficiency / environmentally friendly
- No UV or IR radiation
- 3 year warranty



S9389

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9389	045923093890	120	6.5	60W	0.92	PAR16	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	6.5PAR16/LED/40'/5000K/120V	Dimmable	Compatible dimmers for S9389	2-7/8"	2.00"	500	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	CEC Status
5000	Natural Light	80	40	-25C (-13F) to a maximum of +45C (+113F)	48	Box	Non-Compliant

RoHS Compliant		UL or ETL Listed		Warranty			
Yes		Yes		5 Year Limited - 10 hour use per day			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051