



GE
Lighting

76045 - GE LED A21

LED12DA21/840

☞ GE LEDs offer outstanding energy efficiency, long-lasting performance and just-right brightness, all in one package. They illuminate your home with a bluish-white light that creates a cool appearance. Use this GE LED general purpose light in table lamps, sconces and open fixtures. It's great for frequently used fixtures—GE LED's long life and low energy use will help you save money on energy.

☞ Energy Star Rated

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Dimmable	Yes
Lamp Type	A21
Primary Application	General Purpose
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Dimmable / Non-Dimmable	Yes
Lamp Count	1
Life in Years	13.7 yr
Replacement Watts	0 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.45
Base	E26
Bulb Shape	A21

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	1100 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

PRODUCT INFORMATION

Product Code	76045
Description	LED12DA21/840
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168760454
Standard Package GTIN	00043168760454
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168760454
Standard Package GTIN	10043168760451
No Of Items Per Sales Unit	
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	

DIMENSIONS

Bulb Max Overall Length-MOL	5.16 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V
Rated power (Watts)	12 W