



Hoffman

Clamp Cover, Type 4X

Catalog Number: A1614NFSS6
US List Price (USD): \$911.70

Bulletin Number:

- A51S



Model Code:

- 83540

Ship Wt. Std. Pkg. (lbs):

- 19.0

IP Rating:

- IP66

UL Listed:

- 50, 50E

Industry Standards:

UL 50 Listed; Type 3R, 4, 4X, 12; File No. E27525 cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E27525 UL 508A, 508 Listed; Type 3R, 4, 4X, 12; File No. E61997 cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997 NEMA/IEEMAC Type 3R, 4, 4X, 12, 13 CSA File No. 42184: Type 4, 4X, 12 IEC 60529, IP66 *Meets Type 3RX requirements*

Description

Used in either corrosive or outdoor applications, Clamp Cover Enclosures combine a seamless foam-in-place gasket with stainless steel screw-down clamps for a consistent and reliable seal, yet the cover is easily removed for access and modifications.

Applications:

Used in either corrosive or outdoor applications, Clamp Cover Enclosures combine a seamless foam-in-place gasket with stainless steel screw-down clamps for a consistent and reliable seal, yet the cover is easily removed for access and modifications.

Specifications:

- 16 and 14 gauge Type 304 or 316L stainless steel
- Seams continuously welded and ground smooth
- Seamless foam-in-place gasket
- Stainless steel screws and clamps
- Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger
- Bonding provision on door and body

Finish:

Cover and sides of body have smooth #4 brushed finish.

Accessories:

- Terminal Block Kit Assembly for Junction Boxes Overview
- Fast-Operating Clamp-Cover Junction Box Clamp
- Panels for Junction Boxes
- Steel and Stainless Steel Window Kits

Modifications and Customizations:

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

Notes:

- A404NFSS, A404NFSS6, A6044NFSS and A6044NFSS6 are UL 508A Listed.
- The remaining catalog numbers are UL 50 Listed.
- Catalog numbers ending in "6" are Type 316L stainless steel.
- Purchase panels separately. Optional stainless steel, composite and aluminum panels are also available for most sizes.
- Reference the Specification Sheet for Popular Accessories.

Technical Data


Clamp Cover, Type 4X

Catalog Number	A1614NFSS6
A in.	16
B in.	14
C in.	6
title	A1614NFSS6 : J Box, Type 4X Clamp Cover
Type Number	Type 4X
F in.	5.5
Panel Size D x E in.	14.75 x 12.88
J in.	5.56
M in.	—
N in.	2.38
V in.	0.25
T in.	13
Overall L x W in.	17.50 x 15.38
Steel Panel	A16P14
Mounting G x H in.	16.75 x 12.00
Y in.	0.62
Cover Gauge	16
Body Gauge	14
Conductive Steel Panel	A16P14G


Certifications

 EU Certification

 UL Certification

 Declaration of Compliance

Documents

 Spec Sheet

















 Instruction Manual

 3D STEP CAD

 2D DXF CAD

 Dimension Drawing

Accessories

Item			
	Panels for Junction Boxes	A16P14	
	Clamp Cover, Type 4X	A1614NFSS6	
	Clamp Cover, Type 4X	A1614NFSS6	
	Panels for Junction Boxes	A16P14G	
	Panels for Junction Boxes	A16P14AL	
	Fast-Operating Clamp-Cover Junction Box Clamp	AL23SS	
	Padlock Kit for Junction Boxes	APLKJIC6SS	
	Panels for Junction Boxes	A16P14SS	
	Clamp Kits	AL18	
	Junction Box and Wall-Mount Enclosure Swing-Out Panel Kit	AJCDFK	
	Terminal Block Bracket Assemblies for Junction Boxes	A14JTMA	
	Composite Panels for Junction Boxes and UL/NEMA Wall-Mount Enclosures	A16P14C	
	Terminal Box Straps for Junction Boxes	A16JS	
	Terminal Box Straps for Junction Boxes	A14JS	
	Terminal Block Strips for Junction Boxes	A16JBNS	
	Terminal Block Strips for Junction Boxes	A14JBNS	