



89807-12: One Light Outdoor Wall / Ceiling Mount



Collection: Bayside

UPC #:785652040528

Finish: Black (12)

Dimensions:

Diameter:	10"	Extends:	5"
Height:	5"	Wire:	6 1/2" (color/Black/White)
Weight:	1.8 lbs.	Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box

Bulbs:

1 - Medium A19 75w Max. 120v - Not included

Features:

- Fixture may be mounted on wall or ceiling.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Polycarbonate - Black

Safety Listing:

Safety Listed for Wet Locations
Safety Listed for Wet Locations

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Polycarbonate	Frosted Ribbed	1									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate					5	

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	89807-12	1	785652040528	10.5	10.75	6.25	0.408	2.2	175	Yes
Master Pack	89807-12	12	10785652040525	22.75	19	22	5.503	29.2	175	Yes
NJ Pallet		144		48	40	77	85.556	350.4		No
NV Pallet		144		48	40	77	85.556	350.4		No