

PRODUCT SPECIFICATION

GENERAL INFORMATION:

Catalog number: See table below

Description: 6/2 & 8/1 SRDT, 125/250V 50A range power supply cord

kit with flanged spade terminals and metal strain relief

Approvals: UL Listed

CONSTRUCTION PARAMETERS:

Cable type: SRDT, flat, gray


Insulation and jacket material: PVC, integral insulation and jacket

Conductors: (2) 6 AWG & (1) 8 AWG, bare copper

Conductor identification: Center conductor (8 AWG neutral) is ribbed

Overall cable dimensions (nom): 1.025 x 0.400"

Temperature rating: -20 to +60 deg C



Note: Plug style may vary

Plug configuration: NEMA 10-50P

Plug electrical ratings: 125/250 VAC, 50A

Plug material: PVC, gray

Terminals: 1/4" flanged spade

Strain relief: Metal, included but not attached

CATALOG NUMBERS:

Length	Catalog number
4 ft	09014
5 ft	09015
6 ft	09016

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without the written consent of Coleman Cable Inc.