



S9764

12W/LED/PAR30/LN/3K/100-277V
12 watt PAR30 Long Neck LED; 3000K; 25' beam spread;
Medium base; 100-277 volts

Features

- High efficiency 100LPW
- Replaces Halogen and ceramic metal Halide lamps
- Long life
- Non-dimmable



S9764

Item Number	UPC	Voltage	Watts	Operating Frequency	Lamp Shape	Base	ANSI Base
S9764	045923097645	120-277	12	50/60Hz	PAR30LN	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
12W/LED/PAR30/LN/3K/100-277V	Non-Dimmable	White	4-5/16"	3-3/4"	1200	50000	3000

Color	CRI	Beam Spread Deg	Package Type	ENERGY STAR	CEC Status	RoHS Compliant	UL or ETL Listed
Soft White	83	25	Box	ENERGY STAR	Non-Compliant	Yes	Yes

UL Classification	Warranty
cULus - Dry Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

