

Features & Benefits

- Internal Driver
- Smooth, Consistent Light
- UL for Safety
- No UV, No Mercury
- Long Life
- High CRI
- Instant on, no delay or warm up time
- Convenient and quick installation
- Utilizes non-shunted(rapid start) sockets
- Compatible with controls and sensors
- Works in cold temperature applications
- 5 Year Warranty



Flex™

Internal Driver LED FT Lamp

Commercial Grade LED FT Lamp

Specification Data

Model No.	Replace	Lamp Wattage	Input Voltage	CCT	Initial Lumens	CRI	Lamp Efficacy	Life
LT36W/835-ID FT36W 15			120-277	3500 1200		83 80		50000
LT36W/840-ID FT36W 15			120-277	4000 1200		83 80		50000
LT36W/850-ID FT36W 15			120-277	5000 1200		83 80		50000

Wiring diagram



LT series	Overall Length (cm)	Base face to top (cm)
LT40	54.00	49.30
LT36	42.10	37.40
LT24	32.60	27.80
LT18	23.10	18.30