



6519-98: One Light Pendant



Collection: Painted Shade Pendants

uses Black Cord

UPC #:785652651984

Finish: Brushed Stainless (98)

Dimensions:

Diameter: 15 3/4"

Height: 8 1/4"

Weight: 3.9 lbs.

Overall Height: 62 1/4"

Wire: 54" (color/Black)

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 1 - Medium G40 150w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Stainless

Safety Listing:

Safety Listed for Dry Locations
Safety Listed for Dry Locations

Instruction Sheets:

English (HC-103)
French (F-004)

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1			5		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	6519-98	1	785652651984	17	17	9.75	1.631	5	250	Yes
NJ Pallet		40		48	40	73	81.111	200		No
NV Pallet		40		48	40	73	81.111	200		No