



UPC Code: 078477796979

Country Of Origin: China

NEMA:
5-15R



RGF15-RN

Leviton Renu® Tamper-Resistant Self-Test SmartlockPro GFCI Outlet RGF15-0RN, 15A-125V, in Rich Navy

Renu in a snap! Renu is the smart new line of decorative electrical products from Leviton. Install Renu and get a fresh stylish look, plus the ability to change the color of any Renu device when you update a room. Designed for do-it-yourselfers, the line includes switches, outlets, GFCIs, dimmers, and sleek, screwless wallplates available in 20 designer colors to blend in or contrast with your decor. Refresh the color of any Renu device in a snap, without any rewiring or the need for an electrician. Just order a color change kit in the color you want, snap off the faceplate on the device and snap on the new face. Add a coordinating wallplate (sold separately) to finish the look. Renu fits your lifestyle and adapts to your changing taste.

Technical Information

Environmental Specifications

At Rated Voltage: 1 HP

Operating Temperature: 0°C to 40°C

Product Features

Amperage: 15 A

Brand: Renu

Color: Rich Navy

Color Change Kit: RKG15

Dielectric Voltage: Withstands 1250VAC per UL 943 and CSA-C22.2 No. 144.1-06

Feature: Renu Self-Test GFCI

Flammability: Rated HB or better UL94

Grade: Residential/Commercial Specification Grade

Grounding: Self-Grounding Clip and Green Ground Screw

NEMA: 5-15R

Pole: 2

Standards and Certifications: cULus

Strap Material: Galvanized Steel

Tamper Resistant: Yes

Termination: Back & Side

Trip Level: Class A, 5mA plus or minus 1mA

Type: GFCI

Voltage: 125 VAC

Warranty: 2-Year Limited

Wire: 3

Electrical Specifications

Body Material: Polycarbonate

Clamps: Brass

Dielectric Voltage: Withstands 1250VAC per UL 943 and CSA-C22.2 No. 144.1-06

Face Material: Thermoplastic

Flammability: Rated HB or better UL94

Grounding Screw: Plated Steel

Line Contacts: Brass Double Wipe .031 Thick

Notes: Wallplate Sold Separately

NOM: Yes

Product ID: Ratings are permanently marked on device

Terminal Accom.: 14-10 AWG

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral

UL 498: Yes

AC Horsepower Ratings

Amperage: 15 A

At Rated Voltage: 1 HP

Brand: Renu

Color: Rich Navy

Color Change Kit: RKG15

Feature: Renu Self-Test GFCI

Grade: Residential/Commercial Specification Grade

Grounding: Self-Grounding Clip and Green Ground Screw

Pole: 2

Standards and Certifications: cULus

Strap Material: Galvanized Steel

Tamper Resistant: Yes

Termination: Back & Side

Trip Level: Class A, 5mA plus or minus 1mA

Type: GFCI

Voltage: 125 VAC

Warranty: 2-Year Limited

Wire: 3

Material Specifications

ANSI: C-73

Body Material: Polycarbonate

CSA C22.2 No. 42: Yes

Clamps: Brass

Face Material: Thermoplastic

Grounding Screw: Plated Steel

Line Contacts: Brass Double Wipe .031 Thick

NEMA: WD-6

NOM: Yes

Short Circuit Current Rating: 10KA
Temperature Rise: Max 30C after 100 cycles OL at 150 percent rated current
Terminal Screws: Plated Steel
Yoke: Zinc-Plated Steel

Standards and Certifications

ANSI: C-73
CSA C22.2 No. 42: Yes
NEMA: WD-6

Notes: Wallplate Sold Separately

Terminal Screws: Plated Steel

Yoke: Zinc-Plated Steel

Mechanical Specifications

Product ID: Ratings are permanently marked on device

Terminal Accom.: 14-10 AWG

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts/

