



## 8039-12: Two Light Outdoor Wall Lantern



**Collection:** Lancaster

Medium Solid Brass Classic Two Light Wall Lantern in Black Finish and Clear Curved Beveled Glass.

Solid brass classic two light wall lantern in black finish and clear curved beveled glass.

**UPC #:**785652803901

**Finish:** Black (12)

### Dimensions:

**Width:** 10"

**Height:** 20 1/2"

**Extends:** 9 1/2"

**Wire:** 6 1/2"

**Mounting Proc.:** Cap Nuts

**Connection:** Mounted To Box

**Bulb Appearance:** Clear

### Bulbs:

2 - Candelabra Torpedo 40w Max. 120v - Not included

### Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

1 Body - Brass - Black

### Safety Listing:

Safety Listed for Wet Locations  
Safety Listed for Wet Locations

### Instruction Sheets:

English (HC-231)  
French (F-009)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear Curved Beveled	6									

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	9 1/4	4 1/2	3/4		9 1/2	11

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8039-12	1	785652803901	11.75	11.75	23.75	1.898	10.95	150	Yes
NJ Pallet		36		48	40	72	80	395		No
NV Pallet		36		48	40	72	80	395		No