



A19 MODELS

| MODEL NO. | INPUT POWER (W) | ССТ | DELIVERED LIGHT OUTPUT (LM) |
|------------------------|--------------------|-------|--------------------------------|
| A19-9W30KD-L7-LS | 9 | 3000K | 800 |
| A19-9W50KD-L7-LS | 9 | 5000K | 800 |
| A19-11W30KD-L7-LS | 11 | 3000K | 1100 |
| A19-11W50KD-DEC-L7-LS* | 11 | 5000K | 1100 |
| A19-15W30KD-L7-LS | 15 | 3000K | 1600 |
| A19-15W50KD-L7-LS | 15 | 5000K | 1600 |

^{*}Suitable for enclosed fixture

LED Dimmable Omnidirectional A19

Forest Lighting omnidirectional and dimmable LED A19 bulbs are ideal for hotels, restaurants, apartments and other residential buildings. With an emission angle of over 300°, they provide comfortable diffused light with no unnatural shadows. Forest Lighting LED A19 Lamps are offered in 9W, 11W and 15W that replace 60W, 75W and 100W incandescent bulbs, respectively, saving a tremendous amount of energy.

FEATURES & BENEFITS

- Omnidirectional, >300° beam angle
- Natural A-lamp shape
- Dimmable
- Ideal for hotels, restaurants and residential buildings
- Models equivalent to 60W, 75W and 100W incandescent bulbs
- Rated lifetime of 25,000 Hrs
- Energy Star listed for rebates

WARRANTY
3 Year Warranty



LISTINGS AND CERTIFICATIONS







LED Omnidirectional A19


SPECIFICATION INFORMATION


| Input Power | 9W (60W equivalent), 11W (75W equivalent), 15W (100W equivalent) |
|---------------|---|
| Input Voltage | 120V / 60Hz |
| Power Factor | > 0.9 |
| Base Type | E26 |

OPTICAL SPECIFICATIONS

| Correlated Color Temperture (CCT) | 3000K, 5000K |
|-----------------------------------|--------------|
| Color Rendering Index | >80 |
| Beam Angle | >300° |

MECHANICAL SPECIFICATIONS





ORDERING INFORMATION


Example: A19-11W30KD-L7-LS

| Product | Nominal Input Power | CCT | D-L7-LS |
|---------|---------------------|------------------|------------|
| A19 | 9W 9W | 30K 3000K | D-L7-LS |
| | 11W 11W | 50K 5000K | DEC-L7-LS* |
| | 15W 15W | | |

^{*}DEC-L7-LS only for model A19-11W50KD-DEC-L7-LS

LED Omnidirectional A19

PHOTOMETRY





Performance Data

| Delivered Lumens (Ims) | 813 |
|------------------------|------|
| Input Wattage (W) | 8.75 |
| Efficacy (LpW) | 92.9 |
| Voltage (V) | 120 |
| | |

LED Omnidirectional A19

PHOTOMETRY





Performance Data

 Delivered Lumens (Ims)
 1159

 Input Wattage (W)
 10.8

 Efficacy (LpW)
 107.3

 Voltage (V)
 120

Performance Data

 Delivered Lumens (Ims)
 1635

 Input Wattage (W)
 14.98

 Efficacy (LpW)
 109.2

 Voltage (V)
 120