

MINKA-LAVERY®

Item #	UPC Code:
3066-84	747396101095
Product Family Name:	Finish:
Via Capri	Brushed Nickel
Category:	Category Type:
ISLAND LIGHTS	Island Light
Certification	
3057374	
Patents:	
Notes:	



Image File Name: 3066-84.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
17.75	32	12.5	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
Yes	20.5	56.5	Yes
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight:
72		No	14.97
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom:
5.0	0.63	9.75	
Backplate Width:	Backplate Height:	Center to Top:	

LAMPING

No. of Bulbs:	Light Type:			
6	B10.5 CAND			
Max Bulb Wattage:	Socket:			
60	E12 CAND			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Bulb/LED Included:
Yes			No	
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material:
Clear Wood Grain Water	GLASS
Part No.:	Quantity:
G3066	4
Width:	Height:
5.75	10.25



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
20.25	8.5	25.0	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
18.37	2.49	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1



ETL
Intertek

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.