



Carlon®

Specialty Electrical Boxes
T&B Catalog Number:

FN-23

UPC Number:

78599102069

Status:

Active

Description:

One-Gang Vapor-Tight Box, Volume 22.5 Cubic Inches, Length 3-5/8 Inches, Width 2-1/4 Inches, Depth 3-5/8 Inches, Color Black, Material Polycarbonate, Mounting Means Angled Side Nails

Features

Drywall flange covered with a foam gasket and additional gaskets over the cable entry points that provide a vapor-tight seal, preventing the free flow of air through the box.

High strength polycarbonate construction, will not shatter when cold or distort in heat.

1/2 in. offset flange to ensure a flush fit in 1/2 in. drywall.

Angled side nails for rapid installation.

Pre-drilled flanges for additional mounting options.

General

Material	Non-Metallic
Color	Black
Wiring System	Non-metallic sheathed cable
Volume (cu.in.)	22.5
Work	New
Mounting Method	Angled side nails
Number of Gangs	1

Dimension Information

Length (inches)	3 5/8
Width (inches)	2 1/4
Depth (inches)	3 5/8

Packaging

Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	26 lbs. per 100

Application Support

Product Overview-Carlon Black PC Boxes Available on Website

Certifications



File Nbr:

E 11461

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125

T&B Technical Support
MS 3B-50
8155 T&B Blvd.

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289

www.tnb.com

Memphis, TN 38125

Fax: (901) 252-1321

Email: techsupport@tnb.com