



Heavy-Duty T&B Catalog Number:

L-18-120-0-L

UPC Number:

72849491273

Status:

Active

Description:

Heavy Duty Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 447.32mm (17.611 Inches), Width of 7.62mm (0.30 Inches), Thickness of 1.91mm (0.07 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

General

Material	Nylon 6.6 Weather Resistant
Color	Black

Dimension Information

Nominal Length (inches)	18
Length (inches)	18.0
Width (inches)	0.300
Max. Wire Bundle Diameter (inches)	4 7/8
Min. Wire Bundle Diameter (inches)	3/16

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Tooling

Application Tools	ERG120
-------------------	--------

Packaging

T&B Order Multiple	500
T&B Inner Pack	50
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1 lbs. per 100

Application Support

Overview	Available on Website
Material Selection Guide	Available on Website
Available Colors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com