## **G25 Globe Incandescent Lamp**

# Item Number 03123

### Specifications

Energy Used (Watts)	60
Domestic Code	60G25/W/VR
Volts	120
Brightness (Lumens)	570
Average Rated Hours	1500
Life (in years)*	1.3
Dimmable	Yes
Filament Type	C9
Estimated Yearly Energy Cost**	\$7.23
Package Type	Вох
Country of Origin	China



### Physical Characteristics

Finish	.White
Base	.Medium (E26)
MOL	.4.38"



Vibration Resistant lamps are designed for vibration service only.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

#### Call 1-800-999-2226 or visit www.westinghouselighting.com.

(W), WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.

<sup>\*</sup>Based on 3 hrs./day

<sup>\*\*</sup> Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.