



Specification Sheet

CA10 Flame Tip Incandescent Lamp

Order Number **03265**

Specifications

Energy Used (Watts).....	40
Domestic Code.....	40CA10
Volts.....	120
Brightness (Lumens)	365
Average Rated Hours	1500
Life (in years)*	1.4
Filament Type	CC2V
Light Center Length (LCL)	2 1/16"
Estimated Yearly Energy Cost**	\$4.82
Country of Origin	China

Physical Characteristics

Finish	Clear
Base	Medium
MOL.....	4"



* Based on 3 hrs./day

** Based on 3 hrs./day 11¢/k/Wh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee
® WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

