



Specification Sheet

BR30 Reflector Incandescent Lamp

Item Number **03646**

Specifications

Energy Used (Watts).....	65
Domestic Code.....	65BR30/FL
Volts.....	120
Beam Type.....	Flood
Filament Type	CC6
Light Center Length (LCL)	3 1/16"
Brightness (Lumens)	650
Average Rated Hours	2000
Life (in years)*.....	1.8
Estimated Yearly Energy Cost**.....	\$7.83
Country of Origin.....	China

Physical Characteristics

Finish	Frost
Base	E26 (Medium)
MOL.....	5 3/8"



* Based on 3 hrs./day
** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com

Westinghouse Lighting Corporation, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting Corporation, a Westinghouse Electric Corporation licensee
© "Westinghouse" and "You can be sure...if it's Westinghouse" are all registered trademarks of Westinghouse Electric Corporation

