

PROJECT: \_\_\_\_\_

FIXTURE TYPE: \_\_\_\_\_

LOCATION: \_\_\_\_\_

CONTACT/PHONE: \_\_\_\_\_



|   |   |
|---|---|
| Model #   | <b>83391</b>                                  |
| Collection                                      | meridian™                                     |
| Finish  | Brushed Nickel                                |
| Shade/<br>Diffuser                              | Clear Etched Acrylic                          |
| FIXTURE:<br>Length/Dia.<br>Width/Ext.<br>Height | 43.25" (110 cm)<br>11" (28 cm)<br>11" (28 cm) |
| Maximum<br>Hanging<br>Height                    | 117.5" (298.5 cm)                             |
| Light Source/<br>Bulb Info.                     | LED Tape 0.1W x 468<br>= 48.8W Total          |
| Included?                                       | Intergrated                                   |
| Driver/<br>Transformer                          | Electronic, Class 2<br>Driver, Dimmable       |
| Input   | 100-120VAC, 50/60<br>Hz, .9A                  |
| Dimmable  | Yes   |
| Color   | 3200K   |
| Lumens  | 1681  |
| Notes:  |   |

