

Hubbell L1530C HUBW NEMA L15-30C CONNECTOR

PRODUCT DETAILS

- Polarized
- L15-30R
- 250 Vac 3 Phase
- 30 Ampere
- 3 Pole
- 4 Wire
- Grounding
- Approval Ul, Csa

L1530C HUBW NEMA L15-30C CONNECTOR

PRODUCT SPECIFICATIONS

Amperage Rating	30A	
Color	Black and White	
Material	Composite	
Mounting	Cord Mounted	
Number of Poles	3-Pole	
Temperature Rating	Maximum Continuous: 75%XDD C; Minimum Continuous: -40%XDD C w/o impact, -25%XDD with impact.	
Type	Hubbell Pro	
Voltage Rating	3-Phase 250V AC	
Application	Heavy Duty	
Approval	UL, CSA	

Commodity Code	51300
Conductor Range	#12AWG to #8AWG
Configuration	L 15-30R
Connection	Screw Terminals
Environmental Conditions	Indoor Dry unless protected by additional means
Ground Type	Grounding
Insulation	Insulated Body
NEMA Rating	L 15-30R
Number Of Conductors	4-Wire Grounding
Size	Standard
Standard	NEMA WD1 and WD5, UL498
Sub Brand	Twist-Lock
UPC	783585840680
UPC11	78358584068
Voltage	250 VAC 3 Phase