Straight Blade Devices

15A, 250V, 2 Pole, 3 Wire Grounding

HBL® Extra Heavy Duty, Specification Grade, Duplex Receptacle

Features

- · Triangle marking on face indicates isolated ground
- · Slender/compact design
- Finder Groove Face
- · Reduces installation time
- · Fully insulated design

Ordering Information

Description	Device Color	UPC	Catalog Number
Isolated ground, back	Orange	783585778556	IG5662

Listings

UL Listed to UL498 File No. E2186 Certified to CSA, C22.2, No. 42 File 285 NEMA® WD-6 Compliant NEMA® WD-6 Compliant

Specifications

Face	Nylon	
Base	PBT	
Mounting Strap	.040" (1) Galvanized steel	
Automatic Self-grounding Clip	Stainless steel	
Ground Contact	.031" (.8) Brass	
Clamp	Nickel plated steel	
Ground Contact	.031 in. (.8) Brass	
Terminal Screws	Brass	
Mounting Screws	Stainless Steel	

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #14-#10 AWG copper stranded or solid conductor only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental


Flammability UL 94 V-2 or better

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)









Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Accessories

Wallplate or Weatherproof Cover Duplex Opening

