



## MILA 53553BN-LED

BRUSHED NICKEL

WIDTH:	24.0"
HEIGHT:	5.0"
WEIGHT:	6.0 LBS
MATERIAL:	STEEL
GLASS:	ETCHED OPAL
SOCKET:	3-4.50W G9 LED *INCLUDED
<b>LED INFO:</b>	
LUMENS:	1275
COLOR TEMP:	3000k
CRI:	90
INCANDESCENT EQUIVALENCY:	3-40w
DIMMABLE:	Yes, on any Incandescent, MLV, ELV, or C-L dimmer.
EXTENSION:	4.0"
TTO:	2.5"
CERTIFICATION:	C-US DAMP RATED
VOLTAGE:	120V
UPC:	640665535600
INSTALL OPTIONS:	UP AND DOWN

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

*life*AGLOW®