



NUVO 62-991

LED Flush Mount Emergency Back-Up Ready EMR
Fixture 14" 120-277V



Fixture Type
Close-To-Ceiling Flush

Collection
No

Style
Utility

Finish
White

Width
14"

Height
4.75"

Shade Description
White

Shade Material
Acrylic

Number of Modules
1-Module

Light Source
Circular LED Module

Lumen Output
1300 Lumens

Wattage
20 Watts

Bulb Type
LED

Bulb Base
Direct Wired

Bulb Included
Yes

Replaceable Light Source
No

Safety Rated
Damp Location

Energy Saver
Yes

Energy Star
Yes

UPC
045923329913

Warranty
5-Year Warranty

Voltage
120-277 Volts

Average Rated Hours
50,000 Hours

Incandescent Equivalent
100 Watts

Lamp Code
14" WH ACRYLIC LED
EMR/120/277

Kelvin Temp
3000K

CRI
90+ CRI

Supplied Bulb
Satco S9783 Circular LED
Module. Optional battery

Dimmable/Non-Dimmable
Yes - Dimmable

Suggested Dimmers
Compatible dimmers for 62-
991 for 120V and Satco model-
S9780 for 277V (not included).