



# Superstrut®

## Pipe Straps, Pipe Clamps & Hangers (Series 700)

T&B Catalog Number:

703 3/4 EG

UPC Number:

61601314363

Status:

Active

Description:

Clamp, Universal, 14 Gauge, Size 3/4 Inch, Pipe Outer Diameter .932 Inches - 1.050 Inches, Electro-Galvanized Steel, For use with Rigid or IMC Conduit, Pipe and Electrical Metal Tubing

### Features

Bolt head is combination slot and hex head for flexibility of attachment

Square nut is captivated on the shoulder for easy one-handed tightening.

Straps are interchangeable with 1-1/2 in. strut, for broader application.

Straps are shipped assembled so counting and sorting are easier.

Pipe and conduit sizes are shown on the strap for easy identification.

### Application

Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.

### General

Trade Size (inches)	3/4
Material	Steel
Finish	SilverGalv
Design Load (lbs)	550
Safety Factor	3

### Dimension Information

Pipe O.D. (inches)	.932 - 1.050
Material Thickness (ga.)	14

### Packaging

Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	12.5 lbs. per 100

### Application Support

Metal Framing Channels-Series 1000	Available on Website
Finishes	Available on Website
Pipes-Clamps & Hangers-Series 700	Available on Website

### Certifications

RoHS Compliance	No
-----------------	----

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321

